



CPBR1040C



40A 10KA Type C SP RCBO 1000mm Fly leads

General	Technical
<p>Box quantity: 5</p> <p>ABC indicator: A</p> <p>GTIN-13 / EAN: 5056199026043</p> <p>Fault current protection (RCD): Yes</p>	<p>Associated standards: BS EN 61009</p> <p>Rated voltage: 220-250V</p> <p>Rated kA: 10</p> <p>Rated current: 40A</p> <p>Frequency: 50-60Hz</p> <p>Wiring system: 1 channel</p> <p>Ambient operating temperature: -5 to 40°C (24hour average not exceeding 25°C)</p> <p>Terminal capacity: 16mm</p> <p>Nature of supply: AC</p> <p>Rated fault current: 30</p> <p>Release characteristic: C</p>

Copyright © 2017 Contactum Limited, Victoria House, 2 Blackmoor Lane, Croxley Green Business Park, Watford, WD18 8GA

Source URL: <https://www.contactum.co.uk/content/cpbr1040c>