


C4AS, Film, Metallized Polypropylene, Power, 0.47 uF, 5%, 630 VAC, 1200 VDC, 70°C, Lead Spacing = 27.5mm

**Dimensions**

L	32mm NOM
H	37mm NOM
T	22mm NOM
S	27.5mm +/-0.4mm
LL	6mm -2mm
F	1.2mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	64

General Information

Supplier:	KEMET
Series:	C4AS
Dielectric:	Metallized Polypropylene
Style:	Radial
RoHS:	Yes
Lead:	Wire Leads

Specifications

Capacitance:	0.47 uF
Capacitance Tolerance:	5%
Voltage AC:	630 VAC
Voltage DC:	1200 VDC
Temperature Range:	-40/+85C
Rated Temperature:	70°C
Dissipation Factor:	0.05%
Max dV/dt:	1568 V/us
Resistance:	4.8 mOhms (100kHz)
Ripple Current:	14 Amps (100kHz 70C), 737 Amps (Peak)