

185A-195A.CPE - LONG HALF-ROUND NOSE PLIERS



Standards :

NF ISO 5745, ISO 5745, DIN ISO 5745, ASME B107.500

Description :

- Narrow, finely serrated tips with oval pipe-grip and side cutting edges.
- Cutting edges for copper and hard steel wire to a maximum specification of 1.6mm 160 kg/mm².
- 185A: straight nose.
- 195A: 40° angled nose.
- High durability Carbon alloy steel, with induction hardened cutting edges.
- Bi-Material ergonomic grips resistant to chemical agents featuring: - Return spring - Tether ready point (Tether point adds 10mm to nominal length)
- Chrome finish for corrosion resistance

References :

	B [MM]	C [MM]	D [MM]	D MAXI [MM]	E [MM]	E1 [MM]	L [MM]	[G]
195A.16CPE	17	50		2,5	3	9	160	177
185A.20CPE	18	75	2,9		3,6	9	200	192
195A.20CPE	18	69	2,9		3,6	9	200	192