

## Technical data sheet

Article number:  
112-03060

T30R



|                                                 |                                                                     |
|-------------------------------------------------|---------------------------------------------------------------------|
| <b>Product Group</b>                            | Cable Ties for outdoor use (UV-resistant)                           |
| <b>Product Family</b>                           | T-Series in PA66W black                                             |
| <b>Material</b>                                 | Polyamide 6.6, UV-resistant (PA66W)                                 |
| <b>Colour</b>                                   | Black (BK)                                                          |
| <b>Application Tool</b>                         | MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP |
| <b>Bundle Ø max.</b>                            | 35.0 mm                                                             |
| <b>Bundle Ø min.</b>                            | 1.5 mm                                                              |
| <b>Flammability</b>                             | UL 94 V2                                                            |
| <b>Halogen-free</b>                             | Yes                                                                 |
| <b>Length (L)</b>                               | 148.0 mm                                                            |
| <b>Min.Tensile Strength</b>                     | 135 N                                                               |
| <b>Operating Temperature</b>                    | -40 °C to +85 °C                                                    |
| <b>Package Content packed in</b>                | pack                                                                |
| <b>Pack Cont.</b>                               | 100 pcs.                                                            |
| <b>Releasable Closure (Yes/No)</b>              | No                                                                  |
| <b>Specifications</b>                           | CAGE Code 53421, VG 95387 Part 4                                    |
| <b>Thickness (T)</b>                            | 1.2 mm                                                              |
| <b>Toothing (Serration)</b>                     | Inside Serrated                                                     |
| <b>UL-File Number</b>                           | E64139                                                              |
| <b>UV-resistant acc. to ASTM D6779 (Yes/No)</b> | Yes                                                                 |
| <b>Variant</b>                                  | Inside Serrated                                                     |
| <b>Weight/Unit</b>                              | 0.0007 kg                                                           |
| <b>Width (W)</b>                                | 3.6 mm                                                              |

