

Doro PhoneEasy® 506

Stylish and practical classic mobile phone for talk and text

Widely spaced, concave keys combined with direct memories and SMS button make this good-looking phone very easy to call and send messages with. A crisp colour display and enhanced sound simplify usage even more. Other practical features include reminders, wake-up alarm, vibrating ringer and one-touch assistance dialling with SMS alerts.

- ✓ Direct memories and SMS button
- ✓ Extra loud and clear sound
- ✓ Security functions



STANDARD FEATURES ON MOST DORO PHONES

- | | | | | | | | | | |
|--|---|---|---|---|---|--|---|---|---|
|  |  |  |  |  |  |  |  |  |  |
| Loud and clear sound | Adjustable frequency | Hearing Aid Compatible | Separated large keys | Adjustable contrast and theme | Adjustable text size | Security functions | Ergonomic design | Easy menu handling | Hide unwanted functions |

Doro PhoneEasy® 506



Main features

Speakerphone	✓
Keylock	✓
Backlit keypad	✓
Assistance button	✓
Key tone	✓
Calculator	✓
Calendar with reminder	✓
Wake up alarm	✓
Remote programming (OTA)	✓

Memories

Call log positions	60
One touch memories	3
Phonebook positions	100
Multiple numbers per contact	✓
List top 10 contacts first	✓

Handset unit display

Colour display	✓
Display size (H x W mm)	28*35
Resolution (H x W pixels)	128*160
Big display text	✓
Adjustable font size	✓
Customisable wallpaper	✓

Sounds & Signals

Polyphonic ringtones	9
Visual ring indicator	✓
Vibrating ringer	✓
Ringer volume settings except off	7
Ringer off setting	✓

Acoustics

Receiving maximum level (dB RLR)	-35
Maximum receiving amplification (dB)	35
Maximum ringer volume (dB(A) at 1 metre)	>83
Microphone mute	✓
Volume settings	7

Ergonomic sound™

Tone control	✓
--------------	---

SMS

SMS	✓
-----	---

Ergonomics

Hide unwanted functions	✓
Separated keys	✓
Handset size (mm)	125.5*51*15.5
Handset weight including batteries (g)	81

Cables & Connections

Headset outlet (3.5mm)	✓
------------------------	---

Powering handset unit

Standby time (up to hours)	500
Talk time (up to hours)	8
Battery included (type)	800mAh Li-ion

Technology

GSM (band)	900/1800
SAR	0.680