



## FLAME HIGH VIS JACKET CLASS 3 4584 FLAM

ART. NO: 125938

Front placket opening with zip to top of collar and concealed snap fastening / 2 bellowed chest pockets with flap and concealed snap fastening, 1 with inside D-ring / 2 front pockets with concealed snap fastening / Inside pocket with button fastening and mobile phone pocket with flap and velcro fastening / Adjustable waist with button / Adjustable cuffs with snap fastening / Extended back / Approved according to EN 61482-1-2 APC 1, EN 61482-1-1 ELIM: 8 cal/cm<sup>2</sup> (see Electric arc table for certified garment combinations for EN 61482-1-2 class 2 and open arc according to EN 61482-1-1), EN ISO 11612 A1 B1 C1 E2 F1, EN ISO 11611 A1 class 1 (see Flame and welding table for certified garment combinations), EN 1149-5 and EN ISO 20471 class 2 in sizes XS-S and class 3 in sizes M-3XL / Certified after 50 washes / Leasing laundry-tested according to ISO 15797 / OEKO-TEX® certified.

**Material:** 75% cotton, 24% polyester, 1% anti-static fibre. In transition to PFAS free.

**Weight:** 365 g/m<sup>2</sup>.

**Color:** F171 High vis Yellow/Navy

**Size:** XS-4XL



EN 11612



EN 11611



EN 1149-5



IEC 61482-2



EN 20471



STANDARD 100  
PPE  
SE 23-211  
RSE



**FRISTADS®**

SIZES MAY VARY BETWEEN COLORS  
Print date: 2025-09-04