

## Datasheet

# RS Pro Black Single Tone Electronic Sounder, 12 → 80 V dc, 97dB at 1 Metre

RS Stock No: **235-405**



## Product Details

RS Pro single tone electronic sounding alarm in black colour, sounds at 97 dB for general automotive and warehouse vehicle applications. This reversing alarm has 12 to 80 V dc voltage rating with reverse polarity protection. It has a strong glass filled nylon housing construction that is fully weatherproofed and pressure washable. The alarm is reliable within a broad temperature range of -30 to +77°C.

## Features and Benefits

- Universal mounting
- Voltage range of 12 to 80 V dc
- Pressure washable and fully weatherproof
- Reverse polarity protected
- Reliable within a broad temperature range (-30 to +77°C)



ENGLISH

### Specifications:

Application Type	On/Off Road Vehicles
Current Type	DC
Housing Colour	Black
Special Features	Pressure Washable & Fully Weatherproof
Standards Met	EMC; RoHS Compliant
Base Length	102 mm
Base Width	41 mm
Decibels at 1 Metre	97 dB
Maximum Decibel	97 dB
Maximum Temperature	+70°C
Minimum Temperature	-30°C
Number Of Tones	1
Housing Material	Glass Filled Nylon
Mounting Style	Universal
Supply Voltage	12 to 80 V dc