

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0191890002](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** Krimptite Butt Splice for 18-22 AWG Wire

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Product Specification 194130103-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family [Splices](#)  
 Series [19189](#)  
 Crimp Quality Equipment Yes  
 Overview [Splices](#)  
 Product Name Butt, Krimptite  
 UPC 800755048735

**Physical**

Barrel Type Closed  
 Insulation None  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 0.726/g  
 Packaging Type Bag  
 Wire Size AWG 18, 20, 22

**Solder Process Data**


Lead-freeProcess Capability N/A

**Material Info**

Engineering Number A-145

**Reference - Drawing Numbers**

Product Specification 194130103-000, PS-19902-011-001,  
 PS-19902-013-001  
 Sales Drawing SD-19189-008



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2020)4578-DC (25  
 June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19189 Series](#)

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
PremiumGrade Hand Crimp Tool	<a href="#">640030100</a>
Crimp Head for the AT-200 Pneumatic Hand Tool	<a href="#">640070100</a>
ServiceGrade Hand Crimp Tool - Ratchet	<a href="#">640160038</a>