

Eaton 138369

Catalog Number: 138369

Eaton xEffect SASY 60i Enclosures Switch- & Controlgear Enclosure. Profile terminal 101x45 mm

General specifications



Product Name	Catalog Number
Eaton xEffect SASY 60i busbar terminal	138369
EAN	Product Length/Depth
4015081351497	154 mm
Product Height	Product Width
45 mm	132 mm
Product Weight	Compliances
1.727 kg	RoHS conform

Product specifications

Used with

Double T profile

Connection

185 mm system

60 mm system

Special features

Termination to busbars

without drilling

Put a spacer between the

laminated copper busbars

when connecting in parallel

Type

185 mm system

60 mm system

Connection

Width clamp

132 mm

Busbar thickness - max

40 mm

Busbar thickness - min

40 mm

Busbar width - max

30 mm

Busbar width - min

30 mm

Conductor cross section - max

3600 mm²

Rated operational current (I_e) - max

3200 A

Functions

Connections

Profile terminal

Rated operation current (I_e)

3200 A

Suitable for

T-rail

Strip conductor connection

Resources

Brochures

[eaton-xeffect-sasy60i-customer-success-story-css-wagner-mueller-en-us.pdf](#)

Catalogs

[eaton-xeffect-sasy-60i-fk4300-1167gb-en-us.pdf](#)

[Product Range Catalog Switching and protecting motors](#)

Certification reports

[eaton-xeffect-sasy-60i-declaration-of-conformity.pdf](#)

Drawings

[eaton-control-panels-xeffect-sasy-profile-terminal-dimensions-006.eps](#)

[eaton-control-panels-xeffect-sasy-profile-terminal-3d-drawing.eps](#)

Rated operational current

3200 A

Terminal capacity (conductor)

23 mm - 45 mm (101x)

3600 mm² (Cu band)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia