



Main

Range of product	Actassi
Product or component type	Equipped sliding 19" data panel
Device presentation	Loaded
Provided equipment	24 RJ45 connectors 2 quick fix 19" mountings
Colour	Dark grey (RAL 7016)
Additional information	Automatic grounding

Complementary

Variant	Basic
Number of port	24 port of STP
Communication network category	6 _A
Cover type	Screened
Mounting support	19" rack
Number of rack unit	1U
Type of connector	S-One
Material	DC01 metal sheet 1.2 mm PA6 plastic part PA66 GF20 plastic part
Width	490 mm
Depth	240 mm
Height	47 mm
Net weight	2.5 kg

Environment

Ambient air temperature for operation	-10...55 °C
Standards	IEC 60297 ISO/IEC 11801:ed. 2.2, 2011 NF C 20-150

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations