

Manifold block
VABM-B10-20S-N14-5-P3
Part number: 576480

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Grid dimension	22 mm
Mounting position	optional
Max. number of valve positions	5
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	521 g
Type of mounting	With through-hole
Pneumatic connection, port 1	1/4 NPT
Pneumatic connection, port 3	1/4 NPT
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy