


Proximity sensor SME-10-SL-LED-24

Part number: 173212

FESTO



General operating condition

Data sheet

| Feature | Value |
|--|--|
| Design | For C-slot |
| Conforms to standard | EN 60947-5-2 |
| Symbol | 00991619 |
| Approval | RCM trademark |
| CE mark (see declaration of conformity) | To EU EMC Directive In accordance with EU RoHS Directive |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC To UK RoHS instructions |
| Note on materials | RoHS-compliant |
| Instructions on use | Support / actuator-sensor overview "The right sensor for the actuator" |
| Measured variable | Position |
| Measuring principle | Magnetic reed |
| Ambient temperature | -20 °C ... 70 °C |
| Repetition accuracy | 0.2 mm |
| Switching output | Contacting, bipolar |
| Switching element function | N/O contact |
| Switch-on time | ≤0.6 ms |
| Switch-off time | ≤0.05 ms |
| Max. switching frequency | 500 Hz |
| Max. output current | 100 mA |
| Max. switching capacity DC | 1 W |
| Voltage drop | 0 V |
| Short circuit current rating | no |
| Overload protection | Not available |
| Operational voltage range AC | 12 V ... 27 V |
| Operational voltage range DC | 12 V ... 27 V |
| Reverse polarity protection | no |
| Electrical connection 1, connection type | Cable with plug |
| Electrical connection 1, connector system | M8x1, A-coded, to EN 61076-2-104 |
| Electrical connection 1, number of connections/cores | 3 |
| Electrical connection 1, type of mounting | Snap-locking Screw-type lock Not rotatable |
| Electrical connection 1, compatible type of mounting | Compatible with latching lock Compatible with rotatable screw-type lock |
| Electrical connection 1, connection pattern | 00991155 |
| Connection outlet orientation | In-line |

| Feature | Value |
|---------------------------------------|--|
| Cable length | 0.3 m |
| Cable sheath colour | Grey |
| Material cable sheath | TPE-U(PUR) |
| Type of mounting | Clamped in C-slot Insertable in the slot lengthwise |
| Tightening torque | 0.1 Nm |
| Mounting position | optional |
| Product weight | 5 g |
| Housing colour | Black |
| Material housing | PPS TPE-U(PU) High-alloy stainless steel |
| Switching status indication | Yellow LED |
| Ambient temperature with moving cable | -5 °C ... 70 °C |
| Degree of protection | IP65 IP67 |
| Insulation voltage | 50 V |
| Immunity to surge | 0.8 kV |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Pollution degree | 3 |