

Features

- 1 Gang
- 2 Way
- Switch
- Urea Mouldings
- White
- Stylish smooth profile plate

RS PRO Plate Switches

RS Stock No.: 0845483



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Fits standard 16mm 1 gang back boxes
- Suitable for domestic and light commercial installations.
- Use on its own or in conjunction with 2 way and intermediate plate switches

General Specifications

Dimensions (mm)	86 (W) x 86 (H) x 25 (D)
Plate Dimensions (mm)	86 (W) x 86 (H) x 9.5 (D)
Plate Fixing Centres (mm)	60.3
Style	Rounded Profile
Anti Microbial Certified	Yes
Warranty (Years)	25

Mechanical Specifications

Termination Type	Screw
Terminal Size (mm)	Ø3.5
Terminal Torque Value (Nm)	0.5
Terminal Capacity - Solid (mm²)	4 x 1.5 or 2 x 2.5
Minimum Back Box Depth (mm)	16
2 Way Switch	Yes
Ingress Protection	IP20
Operational Temperature (°C)	-5 to +40

Electrical Specifications

Frequency (Hz)	50
Inductive Load Rating (AX)	10
Load Rating Comments	Suitable for Fluorescent or Inductive Loads

Approvals

Standards Met	BS EN 60669-1
---------------	---------------