

## ECP-20 UK series

20W plug-in power supply



### Features

- No load power consumption
- Protections: short circuit//overload voltage//overload current
- UK and European versions available
- Compact and light-weight
- Withstands operating environment of 0-40°C
- Efficiencies up to 86%
- 3 year warranty
- External switch mode plug-top power supplies
- Efficiency level V, Conforms to Energy-related Product Directive 2009/125/EC
- Energy saving power supply
- Class II double insulated
- 1.2 metre (approx.) output lead with 2.1x5.5x9.5mm centre positive output connector
- Regulated output
- EMC compliance to EN 55022 Class B

Part number	Voltage	Rated current	Voltage range	Rated power	MTBF
7262836	5V	4A	4.7 ~ 5.3V	20W	100,000hrs min. MIL-HDBK – 217F (25°C)
7262845	7.5V	2.67A	7.1 ~ 7.9V		
7262848	9V	2.22A	8.5 ~ 9.5V		
7262842	12V	1.67A	11.4 ~ 12.6V		
7262851	15V	1.33A	14.25 ~ 15.75V		
7262854	18V	1.11A	17.1 ~ 18.9V		
7262858	24V	0.83A	22.8 ~ 25.2V		

### Mechanical specification

