



DX4 DETACHABLE HOLSTER POCKET TROUSERS

DESCRIPTION

The DX4 Holster Trousers are ergonomically designed and use the targeted placement of dynamic 4X stretch fabrics to give maximum range of movement when working. The trousers feature a high-rise back waistband with side elastication, ensuring protection in all working positions. Pre-bent top loading adjustable knee pad pockets, generously sized front pockets and multi-functional zip thigh pockets offer secure storage of phone, pens and tools. Triple stitching throughout for maximum durability.

COMPOSITION

-  **Titanmill Pro Stretch: 93% Polyester, 7% Elastane, 270g**
-  **65% Polyester, 35% Cotton Ripstop Weft Stretch, 230g**
-  **CorePro: 87% Nylon, 13% Elastane, 245g**
-  **Black 26-48**

FEATURES

- 4-way stretch fabric for ease of movement and added comfort
- High rise back waistband ensures protection in all working positions
- Reflective trim for increased visibility and safety
- Zip off holster pockets for added versatility
- Two tier knee pad pockets allowing two positioning options
- Multiple side zip compartments for secure storage
- 16 pockets for ample storage
- 2 side zip pockets for secure storage
- Smart phone pocket
- Hammer loop for secure storage of work tools
- 2 Back pockets
- 2 Zipped thigh pockets

STANDARDS

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
DX440BKR	BLACK	26-14

FEATURES



HALF ELASTICATED WAIST
Half elasticated waist for a secure and comfortable fit



UPF 40+
40+ UPF rated fabric to block 98% of UV rays



16 POCKETS
16 pockets for ample storage



TECHINCAL INFORMATION



- Do not iron the reflective tape
- Wash dark colours separately
- Wash garment inside out
- Wash garment inside out and fully fastened
- Wash reflective tape on the inside
- Wash with similar colours

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m³)	EAN13	GTIN/DUN14
DX440BKR26	Black	65	45	36	1.137	5850.000	5036108366705	15036108855725
DX440BKR28	Black	65	45	36	1.100	5850.000	5036108326365	15036108815149
DX440BKR30	Black	65	45	36	1.090	5850.000	5036108326372	15036108815156
DX440BKR32	Black	65	45	36	1.120	5850.000	5036108326389	15036108815163
DX440BKR33	Black	65	45	36	1.130	5850.000	5036108326396	15036108815170
DX440BKR34	Black	65	45	36	1.140	5850.000	5036108326402	15036108815187
DX440BKR36	Black	65	45	36	1.170	5850.000	5036108326419	15036108815194
DX440BKR38	Black	65	45	36	1.170	5850.000	5036108326426	15036108815200
DX440BKR40	Black	65	45	36	1.190	5850.000	5036108326433	15036108815217
DX440BKR41	Black	65	45	36	1.220	5850.000	5036108326440	15036108815224
DX440BKR42	Black	65	45	36	1.200	5850.000	5036108326457	15036108815231
DX440BKR44	Black	65	45	36	1.220	5850.000	5036108326464	15036108815248
DX440BKR46	Black	65	45	36	1.307	5850.000	5036108326471	15036108815255
DX440BKR48	Black	65	45	36	1.270	5850.000	5036108326488	15036108815262