



Product data sheet

Power tools for trade & industry

Cordless Impact Wrench

PRO GDS 18V-1050 H



Full power at its best: 3/4" high torque impact wrench with BITURBO Brushless technology

The most important data

Battery voltage	18.0 V
Torque, max.	1,050 Nm
No-load speed	0-800 rpm

Part Number 0 601 9J8 500

Technical data

Technical data

Torque adjustment range, min./max., 1st level	0/350 Nm
Torque adjustment range, min./max., 2nd level	0/750 Nm
Torque adjustment range, min./max., 3rd level	0/1050 Nm
No-load speed	0-800 rpm
No-load speed (1st level)	0-800 rpm
No-load speed (2nd level)	0-1,200 rpm
No-load speed (3rd level)	0-1,750 rpm
Torque settings	3
Weight excl. battery	2.9 kg
Torque, max.	1,050 Nm
Impact rate	0-2,600 bpm
Impact rate (1st level)	0-1,600 bpm
Impact rate (2nd level)	0-2,400 bpm
Impact rate (3rd level)	0-2,600 bpm
Battery voltage	18.0 V
Tool holder	3/4" Square
Breakaway torque, max.	1,700 Nm
Packaging dimensions (width x length x height)	266 x 287 x 97 mm

Noise/vibration information

Tightening screws and nuts of maximum permitted size

Vibration emission value ah	13.5 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Impressive power with cordless freedom thanks to ProCORE18V batteries and brushless motor
- High performance motor with a tightening torque of 1,050 Nm and a breakaway torque of up to 1,700 Nm
- Ideal versatility and controlled power due to 3-speed/torque settings

**BITURBO**
BRUSHLESS**AMP** *Share!*
POWER TO
BOSCH

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

