

# Needle nose pliers Professional electric with cutting edge straight shape 200 mm, 8" (26727)



Tools that work for you

Wiha Werkzeuge GmbH  
Obertalstraße 3-7 78136 Schonach  
E-Mail: info.de@wiha.com  
Tel.: +49 (0)7722 959-0



Order no.: 26727

Article number: Z05020006

EAN: 4010995267278

Customs tariff number: 82032000

Increases your efficiency: Extra-long plier head for inserting low-lying components.

Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion.

Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Application: For work in the area of live parts up to 1,000 V AC.

Application: Gripping and holding as well as cutting soft and hard wires and cables. Preferred choice in the electrical sectors.

Standard: Manufactured acc. to IEC 60900.

DIN ISO 5745.

---

Customs tariff number	82032000
-----------------------	----------

---

Blister packed	No
----------------	----

---

Durchmesser max	1.6 mm
-----------------	--------

---

Hardened spring steel	1.6 mm
-----------------------	--------

---

Hard wire	2.2 mm
-----------	--------

---

Medium-hard wire	3.2 mm
------------------	--------

---

Cutting force	17
---------------	----

---

Overall length (mm)	200 mm
---------------------	--------

---

Overall length (Inch)	8"
-----------------------	----

---

VDE article	Yes
-------------	-----

---

Country of origin (ISO 3166-1 Alpha 3)	VNM
---	-----

---

Gewicht VPE in Gramm	224
----------------------	-----

---

