

**ARCANOL-MULTI2-1KG** [↗](#)

Bearing grease

Multi-purpose grease ARCANOL-MULTI2

## Technical information

**Your current product variant**

|                 |      |                       |
|-----------------|------|-----------------------|
| Grease category | MP   | Multi-purpose greases |
| Package size    | 1 KG | 1 kg can              |

**Technical data**

|                      |                         |                                    |
|----------------------|-------------------------|------------------------------------|
| $\vartheta_{O \min}$ | -30 °C                  | Operating temperature, min.        |
| $\vartheta_{O \max}$ | 120 °C                  | Operating temperature, max.        |
| $\vartheta_G$        | 75 °C                   | Upper continuous limit temperature |
| $n \cdot d_M$        | 500.000 mm/min          | Speed of rotation specific value   |
|                      | Lithium soap            | Thickener type                     |
|                      | Mineral oil             | Base oil type                      |
| $\nu_{40}$           | 110 mm <sup>2</sup> /s  | Base oil viscosity at +40°C        |
| $\nu_{100}$          | 11 mm <sup>2</sup> /s   | Base oil viscosity at +100 °C      |
|                      | 2                       | NLGI class                         |
|                      | Multi-purpose grease    | Grease category                    |
| $\rho$               | 0,95 kg/dm <sup>3</sup> | Density                            |
|                      | 1 kg can                | Container                          |
| $\approx m$          | 1,084 kg                | Weight                             |