

Professionally approved products.

## Datasheet

# 111pc Socket, Bit & Spanner Set

RS Stock number [618-9036](#)



### Features

#### Material

Socket, Bits, Spanners, Hex Keys and Accessories: Chrome vanadium steel

#### Finish

Socket, Bits, Spanners, Hex Keys and Accessories: Chrome plated

Combination Spanners: Satin chrome plated

#### Hardness

Heat treated to HRC 38~54 (sockets & accessories), HRC 35~48 (spanners) & HRC 48~52 (hex key)

## Professionally approved products.

### Features Continued

### Contents

- 1 pc- 1/2" Dr. quick release ratchet round head with rubber handle
- 20 pc- 1/2" Dr. shallow socket: (12pt.)
  - Metric: 10, 11, 12, 13, 14, 15, 16 , 17, 18, 19, 20, 21, 22mm
  - Imperial: 1/2", 9/16", 19/32", 11/16", 25/32", 15/16", 1"
- 8 pc- 1/2" Dr. ww sockets: (12pt.)
  - Sizes: 3/16", 1/4", 5/16", 3/8", 7/16", 1/2", 9/16", 5/8"
- 2 pc- 1/2" Dr. 5" & 10" extension bar
- 1 pc- 1/2" Dr. spark plug socket: 13/16" (21mm)
- 1 pc- 1/2" Dr. universal joint (screw type)
- 1 pc- 1/2" Dr. T-bar adapter
- 1 pc- 1/2" Dr. metal spin disc
- 1 pc- 1/4" Dr. quick release ratchet round head with rubber handle
- 18 pc- 1/4" Dr. shallow socket: (6pt.)
  - Metric: 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10mm
  - Imperial: 5/32", 3/16", 7/32", 1/4", 9/32", 5/16", 11/32", 3/8", 1/2"
- 16 pc- 1/4" Dr. deep sockets
  - Metric: 4, 5, 6, 7, 8, 9, 10, 11mm,
  - Imperial: 3/16", 7/32", 1/4", 9/32", 5/16", 11/32", 3/8", 1/2"
- 11 pc- 1/4" Dr. ba sockets: (6pt.) sizes: ba-0, 1, 2, 3, 4, 5, 6, 7, 8, 9, 10
- 13 pc- 1/4" Dr. socket bits
  - Slotted: 4, 5.5, 7mm
  - Phillips: #1, 2, 3, 4
  - Hex: 3, 4, 5, 6, 8, 10mm
- 2 pc- 1/4" Dr. 2" & 6" extension bar
- 1 pc- 1/4" Dr. universal joint (screw type)
- 1 pc- 1/4" Dr. spinner handle w/red(pp) & black TPR double (go-through type)
- 10 pc- Flat type combination wrench (a grade)
  - Metric: 8, 11, 13, 14, 17mm
  - Imperial: 1/4", 3/8", 1/2", 5/8", 3/4"

## Professionally approved products.

### Features Continued

### Contents

3 pc- Short series hex key wrenches: sizes: 1.5, 2, 2.5mm  
 Blow molded case (size:360cm(w) x 350cm(d) x 80cm(h))  
 RS WW& BA sockets go, no-go gauge as below:

Size: (WW)	go	no-go
1/8"	8.59	8.62
3/16"	11.42	11.45
1/4"	13.49	13.54
5/16"	15.39	15.44
3/8"	18.23	18.28
7/16"	21.03	21.08
1/2"	23.62	23.67
9/16"	25.91	25.96
5/8"	28.22	28.32
11/16"	30.63	30.88
3/4"	33.22	33.62

Size: (BA)	go	no-go
ba-10	3.02	3.11
ba-9	3.37	3.48
ba-8	3.90	4.01
ba-7	4.4	4.54
ba-6	4.95	5.09
ba-5	5.62	5.76
ba-4	6.34	6.48
ba-3	7.2	7.35
ba-2	8.28	8.43
ba-1	9.32	9.48
ba-0	10.54	10.72

### Remarks

1. Torque, gauge and overall length meet din standard