



縦横間自在に差し込めるユニークな6個口設計。
USBPD充電機能搭載で、スマートに電源を確保
できる。3m。ホワイト。

TAP-SLIM6UC-3W

スリムタップ (AC6個口・A1+C1・PD33W・3m・ホワイト)

JANコード 4969887791257



仕様

定格容量	14A・125V 合計1400Wまで
PSE適合規格	あり
定格出力	DC5V・3A 【Type-C】DC5V/3A、9V/3A、12V/2.75A、15V/2.2A、20V/1.65A (最大33W) 【USB A】DC5V/3A、9V/2A、12V/1.5A (最大18W) 【Type-C+USB A同時使用時】合計最大DC5V・3A (最大15W)
差し込み口形状	2P
USBポート定格入力	AC100V~125V 50/60Hz
プラグ形状	2P
プラグ仕様	スイング式
絶縁キャップ	あり
差込口タイプ	ノーマルタイプ
差込口間隔	25.4mm
差込口数	6個口
USBポート数	2ポート USB-A×1ポート Type-C×1ポート
電源コード長	3m
コード導体サイズ	1.8スケア (SQ) ×2心、 仕上がり外形寸法約4.2mm×7.6mm VFFコード
二重構造	あり

コード色	ホワイト
主な対応国	日本
保護機能	過電流保護機能あり 自動識別IC機能あり
コードの種類	二重被ふくコード
USB PD (USB Power Delivery) 対応	○
USB PD最大対応出力	33W
製品サイズ	W30.5×D24×H280mm
重量	約399g

特長

縦横どちらの向きでもプラグを差し込める独自設計です。間のスペースも有効活用でき、自由度が高いタップです。

スリムなデザインで、省スペースに設置可能です。デスク周りやリビングでもすっきり使えます。

裏面には滑り止めラバーを搭載しています。安定感があり、使用中もズレにくい仕様です。

180度スイングプラグを採用し、狭い場所でも無理なく差し込めて、取り回しが便利です。

差し込みプラグには絶縁キャップ付きで、トラッキング火災を防ぎ、安全性を高めています。

USB充電機能を搭載しています。USB Type-Cポートは最大33WのPD充電に対応し、急速充電が可能です。

USB Type-CポートとUSB Aポートの同時使用時は合計最大15Wの出力で、複数デバイスを効率よく充電できます。

3mのVFF保護被ふくコードを採用しています。耐久性が高く、安心して使用できます。

Unique six-port design allows for flexible vertical and horizontal insertion. Equipped with USB PD charging functionality, it provides smart power supply. 3m. White.
TAP-SLIM6UC-3W

Features

- This unique design allows for plugging in either portrait or landscape orientation, effectively utilizing the space between devices for greater flexibility.
- The slim design allows for space-saving installation, making it ideal for desks and living rooms.
- The anti-slip rubber backing provides stability and prevents slipping during use.
- The 180-degree swing plug allows for easy insertion even in tight spaces and is easy to handle.
- The plug is equipped with an insulating cap to prevent tracking fires and enhance safety.
- Equipped with USB charging functionality. The USB Type-C port supports PD charging up to 33W for fast charging.
- When using the USB Type-C and USB A ports simultaneously, a total output of up to 15W is available, allowing for efficient charging of multiple devices.
- The 3.0m VFF protective insulated cord is highly durable and reliable.

Specifications

- Rated Capacity: 14A, 125V
Up to 1400W Total
- PSE Compliant
- Rated Output: DC 5V, 3A
 - [Type-C] DC 5V/3A, 9V/3A, 12V/2.75A, 15V/2.2A, 20V/1.65A (Max. 33W)
 - [USB A] DC 5V/3A, 9V/2A, 12V/1.5A (Max. 18W)
 - [Type-C + USB A] Max. Total DC 5V, 3A (Max. 15W)
- Outlet Type: 2-Pin
- USB Port Rated Input: AC 100V-125V 50/60Hz
- Plug Type: 2-Pin
- Plug Type: Swing
- Insulating Cap: Yes
- Outlet Type: Standard
- Outlet Spacing: 25.4mm
- Outlets: 6
- USB Ports: 2
 - USB-A x 1
 - Type-C x 1
- Power Cord Length: 3.0m
- Cord Conductor Size: 1.8mm Square (SQ) x 2 Cores
- Finished Dimensions: Approx. 4.2mm x 7.6mm VFF Cord
- Double-Insulated
- Cord Color: White
- Compatible Country: Japan
- Protection Features: Overcurrent Protection
- Automatic Identification IC
- Cord Type: Double-Insulated
- USB PD (USB Power Delivery) Compatible
- Maximum USB PD Output: 33W
- Product Dimensions: W30.5mm x D24mm x H280mm
- Weight: Approx. 399g