

FEATURES

- **Concealed design:** Provides a clean and unobtrusive appearance
- **304 Stainless Steel construction:** Ensures durability and resistance to corrosion
- **Removable pin:** Facilitates easy installation and maintenance
- **Bolt-On/Rivet fixing method:** Offers secure attachment options
- **90 mm length:** Suitable for a variety of applications
- **REACH and RoHS compliant:** Meets key environmental and safety standards

RS PRO 90 mm Concealed Hinge, 304 Stainless Steel

RS Stock No: 335-156



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

Product Description

This RS PRO concealed hinge is designed for applications requiring a discreet and durable hinge solution. Made from high-quality 304 stainless steel, it offers excellent corrosion resistance, making it ideal for both indoor and outdoor use. The hinge features a removable pin, allowing for easy installation and maintenance.

General Specifications

Fixing Hole Size	5.2 mm
Fixing Method	Bolt-On/Rivet
Hinge Type	Concealed
Holes per Leaf	2
Pin Style	Removable Pin
Product Type	Concealed Hinge

Mechanical Specifications

Length	90 mm
Material	304 Stainless Steel
Thickness	24 mm
Width	23 mm

Approvals

Standards/Approvals	REACH, RoHS
---------------------	-------------