




Switches > Tactile Switches



Contact Current Rating: 50 mA

Actuator Style: Round Actuator

Operating Function: Off (On)

Contact Base Material: Copper Alloy

Switch Contact Plating Material: Silver

Features

Product Type Features

Leg Style	Gull Wing
Switch Connection Type	Printed Circuit Board
Illuminated	Without
Actuator Style	Round Actuator

Configuration Features

Switch Feedback Type	Tactile
ESD Grounding Terminal	Without
Ganged	With
Operating Function	Off (On)
Support Bracket	Without
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single

Electrical Characteristics

Operating Voltage	24 VDC
-------------------	--------



Body Features

Case Material	LCP
Actuator Profile	Extended
Case Color	Black
Actuator Material	PPS
Cover Material	Steel
Actuator Force	160 g[5.64 oz]
Product Orientation	Vertical
Actuator Color	Black

Contact Features

Contact Current Rating	50 mA
Contact Base Material	Copper Alloy
Switch Contact Plating Material	Silver

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Housing Features

Low Profile	With
Process Sealed	No

Dimensions

Button Width	3.5 mm[.138 in]
Product Height	5 mm[.196 in]
Actuator Length	1.4 mm[.055 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C
-----------------------------	-------------

Packaging Features

Packaging Method	Package/Box
------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold





EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 1571295-1 SWITCH,TACT,THRU-HOLE,SEALED	 TE Part # 1571563-7 FSM4JSML=TACT SWITCH,SMT,BULK	 TE Part # 2-1825910-7 FSM14JH=6MM TACT SWITCH, HIGH TEMP	 TE Part # 1571563-1 FSM4JSMXL=TACT SWITCH,SMT, BULK
 TE Part # 1977223-2 FSM2JSMLSTR=6MM TACT SWITCH, SMT 100gf,	 TE Part # 2-1825027-0 FSMRA7JH04=R/A,TACT PB SW,160G	 TE Part # 3-1825910-3 FSM16JAAH=6MM TACT SWITCH, HIG	 TE Part # 1-1825027-1 FSMRA4JH04=R/A,TACT PB SW,160G

FSM4JSMATR

50 mA Tactile Switch, Round Actuator, Off (On), Copper Alloy, Silver Contact Plating, Low Profile, 24 VDC, Alcoswitch FSMJSMA




TE Part # 1571563-6
FSM14JSMAATR=TACT,SMT,T&R




TE Part # 1571625-4
TACT,6X6,SMT,J-LEAD,100GF,T&R




TE Part # 1571627-1
FSM103A=TACT SWITCH,260G




TE Part # 1571563-8
FSM4JSMLTR=TACT SWITCH,SMT,T&R




TE Part # 2-1437565-7
FSM2JSMA=SMT,TACTILE,PB SWITCH



TE Part # 1977263-3
FSM1LPAS=ESD GND SMD TACT SWITCH



TE Part # 1571625-1
TACT,6X6,SMT,J-LEAD,50GF




TE Part # 1571563-4
FSM4JSMAATR=TACTSWITCH,SMT,T&R



TE Part # 1571625-5
TACT,6X6,SMT,J-LEAD,160GF



TE Part # 1571626-2
TACT,SMT,GULL WING,50GF,T&R



TE Part # 1571634-1
TACT SWITCH,SMT,SOFT ACTUATOR




TE Part # 1825965-1
FSMH=3.5 X 6.0 X 5.0 TACT SWITCH, HT

Also in the Series | [Alcoswitch FSMJSMA](#)



[Tactile Switches\(22\)](#)

Customers Also Bought




TE Part #3-2319764-4
E STACK PIANO 8P G LONG T&R PD ON



TE Part #AS220-35PN
RECEPT.BOX MNTG.TYPE 2



TE Part #3-1630186-4
HSA50 R047 5%



TE Part #6-1393225-2
RY900064 (RYA51012)

FSM4JSMATR

50 mA Tactile Switch, Round Actuator, Off (On), Copper Alloy, Silver Contact Plating,
Low Profile, 24 VDC, Alcoswitch FSMJSMA



TE Part #YAS216-26PN-CLNUT0
CONNECTOR BOX MTG
RECEPTACLE CLINCH NUTS

TE Part #5-1393225-4
RY900054 (RYA31024)

TE Part #5-1393225-3
RY900053 (RYA51024)

TE Part #5-1416200-2
V23061A1007X116

TE Part #6-1393225-6
RY900068 (RYA51024)

TE Part #YAS218-35PN-CLNUT0
CONNECTOR BOX MTG
RECEPTACLE CLINCH NUTS

Documents

Product Drawings

FSM4JSMATR=TACT SWITCH 6X6MIL

English

CAD Files

Customer View Model

ENG_CVM_CVM_4-1437565-2_V1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1437565-2_V1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1437565-2_V1.3d_stp.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English

Products for Mobile Equipment

English