

40VMax Orbital Sander XGT

B0007CG

Abrasive paper size 93 x 185 mm

Model B0007CG is a battery powered orbit sander powered by a 40Vmax XGT Li-Ion battery. Excellent maneuverability has been achieved by using a connector-style connection to the battery, reducing the load on hand and further keeping the overall height low.

The main features and benefits are: Connector connection to the battery, Compatible with AWS (Auto-start wireless system), Net type abrasive papers, Pad saver.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Orbits per Minute	6000 - 12000 min ⁻¹
AWS ready	✓
Sanding Pad Dimensions	93 x 185 mm
Dimensions of Clamped Abrasive Sheet	93 x 228 mm
Sanding Orbit Diameter	2 mm
Sound Pressure Level (L _{pA})	77 dB(A)
Product net weight	1,1 kg
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,9 - 3,1 kg
Product Dimensions (L x W x H):	263 x 92 x 106 mm
Vibration Level, Sanding Metal Plate	3,1 m/s ²
Vibration Uncertainty (K Factor),	1,5 m/s ²

User benefits

- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Soft start for smooth start-ups
- Brushless maintenance-free and long-life motor

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing