

1" TORQUE WRENCH PLUS 200 - 1000 NM

- 1" torque wrench
- $\pm 4\%$ accuracy
- 72-teeth ratchet mechanism compliant with DIN 3122
- Twist reverse and quick-release button for socket changes
- 5-degree swing arc for precise adjustments in confined spaces
- Locking device to prevent accidental torque setting changes
- Clear Nm scale for quick and reliable settings
- Ergonomic bi-material handle with hand placement markings
- Delivered in a durable storage case
- Individually tested to ISO 6789 standards with unique serial number and Declaration of Conformance



TengTools 1192P1000 1" torque wrench Plus is designed for precision and durability in professional environments, with a torque range of 200–1000 Nm and an accuracy of $\pm 4\%$. It is intended for heavy-duty tightening applications such as working with truck engines or installing large industrial machinery that requires high torque values. The torque wrench is designed for clockwise fastening of right-hand threads and constructed according to DIN 3122 standard with twist reverse and quick-release button. It features a 72-teeth ratchet mechanism of click-type which provides a 5° swing arc for controlled torque application, which is crucial for securing critical components. A clear Nm scale and locking button enable quick and precise adjustments. The click-type mechanism provides an audible and tactile signal when the required torque is reached, preventing over-torquing. The ergonomic bi-material handle, designed with anti-slip and markings showing where to place the hand, provides both control and comfort during extended use. With a weight of 6050 g and dimensions of 1243 mm in length and 66 mm in width, the wrench is robustly built to be reliable over time. It comes in a sturdy storage case for protection and easy transport, keeping it safe and ready for demanding environments. Each torque wrench is assigned a unique number and individually tested to comply with ISO 6789 standards and comes with a 'Declaration of Conformance' for guaranteed accuracy.

General information

Country of origin: Taiwan
Barcode: 5020385034037
Tariff code Europe: 8204120000
ECCN US: EAR99
ETIM: EC002132
UNSPSC: 27111715

Features

1"

Attributes

Product type: Torque Wrenches
Drive: 1"
Number of teeth: 72
Range: 200-1000 Nm
Scale resolution: 5
Accuracy: $\pm 4\%$
Calibration certificate: Factory
Reverse direction: Twist
Preset: No
Angular gauge: No
Digital: No
Bi-directional: No
Mechanism: Click
Tethering facility: No

Dimensions

Net weight (g): 6050
Width (mm): 66
Length: 1243 mm

DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.

Technical changes and errors may occur. 04-02-2025 09:18



Sandbergsvägen 3
 441 39 Alingsås,
 Sweden