

## PRO Glue Gun EG330 BOX



Ref: 40303008

### Features

- Semi-Industrial glue gun for very intensive use
- High glue output : up to 1600g/h
- Exchangeable nozzle

Glue gun for professional users. Two preset temperatures (185°C and 200°C). High glue output (up to 1600 g/h). Silicon protected nozzle, and extra stable stand. Various types of nozzle are available as optional accessories.

## Product Information

<b>Adjustable temperature:</b>	Yes
<b>Interchangeable nozzles:</b>	Yes
<b>Heating time:</b>	7min
<b>Glue stick diameter:</b>	12mm
<b>Glue output g/h:</b>	1600g/h
<b>Power W:</b>	400W
<b>Width:</b>	87.00
<b>Height:</b>	325.00
<b>Depth:</b>	340.00
<b>Weight:</b>	1870
<b>Use for:</b>	Use for Car industry, carton closing, electronic, wood assembly, furniture, cable fixing
<b>Material:</b>	Top Class ABS and Glass Fiber
<b>Packaging unit:</b>	1
<b>Other:</b>	EG330 220-240V packed in Carton box for all European Languages