

FEATURES

- **Sintered Bronze Material:** Provides high wear resistance and longevity.
- **Flanged Design:** Ensures secure positioning and easy installation.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling significant static loads.
- **0.75 in Bore Size:** Compatible with standard shaft sizes.
- **1 in Outside Diameter:** Fits seamlessly into compact spaces.
- **1-1/4 in Width:** Offers stability and support for rotational movement.

RS PRO 0.75 in Flanged Plain Bearing

RS Stock No: 528-866



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 0.75 in Flanged Plain Bearing is designed for applications requiring reliable and efficient rotational movement. Made from sintered bronze, this bearing offers excellent durability and performance under varying load conditions. Ideal for use in machinery where space is limited, its compact design ensures seamless integration.

General Specifications

Bore Size	0.75 in
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	1 in
Width	1-1/4 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

