

Kettle XGT®

KT001G

40Vmax

Cordless Kettle powered by XGT® 40Vmax Batteries x 2 (in parallel) for worksites.

KT001G is a excellent choice if you need to boil water without AC power. Compact and lightweight structure. Boiling time (approx.) of 0,8 L water: 8 minutes (23 degrees °C water); 9 minutes (10 degrees °C water). Power is turned on only when the base is grounded.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Tank Capacity for Liquids	0,8 L
Tool weight with battery	2,8 - 5,9 kg
Product net weight	2,1 kg
Product Dimensions (L x W x H):	233 x 322 x 307 mm

User benefits

- Water can be boiled without fire even at job sites where AC socket is not available
- Auto shut-off after boiling with warning buzzer
- Equipped with an anti-spill lock button to minimise accidental spilling of hot water
- Battery protection circuit protects against overloading, over-discharging and over-heating



Related products

Other

User manual

Parts drawing