

Connecting terminal 3VA



Model	
product brand name	SIVACON S4
product designation	connection terminal 3VA
design of the product	40 x 3 mm
design of the surface	other
General technical data	
design of pole	1
design	individual part
suitability for use	for cable terminals
RAL color number	other
color	miscellaneous
Product details	
product component	
• cable entry	Yes
• lock	No
Mechanical Design	
height	50 mm
width	100 mm
depth	50 mm
installation width for cabinet installation	87 mm
installation depth for cabinet installation	50 mm
shape of inner subdivisions	
• shape 2a	No
• shape 2b	No
• shape 3a	Yes
• shape 3b	Yes
• shape 4a	No
• shape 4b	No
mounting position	horizontal
net weight	0.3 kg
material	plastic
Certificates	
reference code according to IEC 81346-2	UC
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



[Confirmation](#)

Environment

[Environmental Conformations](#)

[Environmental Conformations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ5000-4BA58>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ5000-4BA58>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ5000-4BA58

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

1/19/2024 

