



PRODUCT-DETAILS

OHG45H9K

OHG45H9K HANDLE



概要信息	
产品型号	OHG45H9K
产品ID	1SCA022399R7640
欧洲商品编号(EAN)	6417019148847
目录说明	OHG45H9K HANDLE
详细描述	IP65, NEMA 1, 3R, 12, padlockable with three padlocks in OFF-position, door interlock in ON- position. Screw fixing from the back side of the handle. No screws on the front ensures double insulation. The type and the ordering numbers are for one piece, red-yellow.

Material Compliance	
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201
RoHS信息	1SCC011020D0201
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Popular Downloads	
数据手册，技术资料	1SCC301020C0201
说明书和手册	No Instructions and Manuals needed

环境条件	
防护等级	IP65

订货信息	
最小起订量	1 piece
海关关税号	85389099
原产地	Estonia (EE)

尺寸	
产品净宽	78 mm
产品净高	45 mm
产品净深	66 mm
产品净重	0.12 kg

包装信息	
1级包装单元	bag 1 piece
1级包装宽度	45 mm
1级包装长度	80 mm
1级包装高度	66 mm
1级包装 总重	0.14 kg
1级包装 EAN	6417019148847

技术参数	
颜色	Grey
防护等级	IP65
Handle Color	Grey
手柄长度	45 mm
手柄类型	Pistol
Lock Type	Yes
特殊功能	H9K

认证及声明（文件编码）	
符合性声明 - CE	1SCC390030D2704

分类	
对象分类代码	N/A
ETIM 8	EC000229 - Handle for power circuit breaker
ETIM 9	EC000229 - Handle for power circuit breaker

e级	V11.1 : 27370414
WEEE 类别	Product Not in WEEE Scope

分类

低压产品及系统 → 开关类产品 → 隔离开关
低压产品及系统 → 产品服务 → 备件服务 → Parts
低压产品及系统 → 低压系统 → IEC - Low Voltage Motor Control Centers → MNS 3.0 - MCC

