



## outdoor floodlight XLED home 3 SL Sensor-Switched Floodlights

### Information copy

**The mega floodlight in the slave version.** STEINEL sensor-switched LED floodlight XLED home 3 SL, ideal for porches, driveways, courtyards, gardens. 18?W for 1426 lumens of light, STEINEL LED lighting system, 30-year lifespan (average of ?4.5 h/? day), never change a bulb again, Active Thermo Control, colour rendering index Ra > 80, tilting / turning light panel.



### Details

#### STEINEL LED lighting system.

Efficient, long-lasting and trendsetting. More quality of life, more safety and security and more energy saved with intelligent sensor and LED technology from STEINEL.

**Now 25% more light for the same amount of electricity.** Any need to say more than 1426 lumens? This is the most powerful LED floodlight in the STEINEL range impressively showing off 18 W in a way unmatched by any other. And it saves no end of energy into the bargain. Providing day-bright illumination, it consumes a fraction of the energy used by a comparable halogen floodlight. And if that's not enough as a convincing argument, here's another: the highly efficient LEDs are extremely long-lasting thanks to Active-Thermo-Control. In plain language: a good 30 years of life without ever changing a bulb. More output. More efficiency. Less consumption of energy and resources. With its light panel that turns through 180° and tilts through 120°, the LED floodlight can be aimed exactly as required. STEINEL XLED home 3 SL floodlights make the ideal team players for interconnecting several LED floodlights with power LED floodlight STEINEL XLED home 3 SL with sensor. Including 3-year STEINEL functional warranty."



LED-System  
included



UV-protected  
material



Colour rendering  
index ??? 80

### Technical specifications outdoor floodlight X LED home 3 SL Black

European Article Number (EAN)

4007841006884

<b>Dimensions (h x w x d):</b>	234 x 206 x 180 mm
<b>Power connection</b>	230-240 V/50 Hz
<b>Output</b>	18 W max.
<b>Brightness</b>	1426 lm
<b>Efficiency</b>	79.2 lm/W
<b>Light colour</b>	6700 K / SDCM 6
<b>Colour rendering</b>	Ra ≥ 80
<b>LED life expectancy</b>	50.000h (L70B10 to LM80) h
<b>LED cooling system</b>	Active & Passive Thermo Control
<b>Tilting range</b>	180° horizontally, 120° vertically
<b>IP rating</b>	IP44
<b>Protection class</b>	I
<b>Material</b>	UV-resistant plastic with aluminium heat sink
<b>Version</b>	Black
<b>Temperature range</b>	-20 - +40°C
<b>Lamp</b>	STEINEL LED system
<b>With lamp</b>	Yes
<b>Lamp replaceable</b>	No

### **Application**

under porches, driveways, courtyards, gardens.  
Ideal addition to XLED home 3.