

M18 CCS66-502X | M18 FUEL™ 66mm circular saw for wood and plastics

Article: 4933451385



- Milwaukee® designed and built brushless POWERSTATE™ motor for up to 3x longer motor life and up to 2x more cuts per charge.
- Integrated dust blower keeps cut line clear.
- Hang hook allows safe storage of the tool.
- Integrated battery fuel gauge & LED light.
- Flexible battery system: works with all Milwaukee® M18™ batteries.
- REDLINK PLUS™ intelligence system delivers an advanced digital overload protection for tool and battery and uniquely enhances the tool performance under load.
- REDLITHIUM-ION™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life.

M18 CCS66-502X	
Sound pressure level (dB(A))	83.2
Sound pressure level uncertainty (dB(A))	1.5
Sound power level (dB(A))	94.2
Sound power level uncertainty (dB(A))	3
Bore size (mm)	30
No load speed (rpm)	5000
Vibration sawing of wood [m/s ²]	2.0
Vibration sawing of wood uncertainty [m/s ²]	1.5
Voltage (V)	18
Battery pack capacity (Ah)	5.0
Battery type	Li-ion
Supplied in	HD Box
Charger supplied	59 min
No. of batteries supplied	2
Blade diameter (mm)	190
Article Number	4933451385
Weight with battery pack (kg)	4.2
Max. cutting depth 45° (mm)	48
Max. cutting depth 90° (mm)	66