



SIMATIC ET 200SP HA, bus adapter BA 2xRJ45, 2 RJ45 sockets for PROFINET



General information			
Product type designation	BA 2x RJ45		
Interfaces			
Number of PROFINET interfaces	1; 2 ports (switch) RJ45		
Supports protocol for PROFINET IO			
• Number of RJ45 ports	2		
Cable length			
— Cu conductors	100 m		
Ambient conditions			
Ambient temperature during operation			
• min.	-40 °C		
• max.	70 °C		
• horizontal installation, min.	-40 °C		
• horizontal installation, max.	70 °C		
• vertical installation, min.	-40 °C		
• vertical installation, max.	60 °C		
Dimensions			
Width	20 mm		
Height	69.5 mm		
Depth	59 mm		
Weights			
Weight, approx.	46 g		
Classifications			
		Version	Classification
	eClass	14	27-24-26-92
	eClass	12	27-24-26-92
	eClass	9.1	27-24-26-92
	eClass	9	27-24-26-92
	eClass	8	27-24-26-92
	eClass	7.1	27-24-26-92
	eClass	6	27-24-26-92
	ETIM	10	EC002584
	ETIM	9	EC002584
	ETIM	8	EC002584

## Approvals / Certificates

## General Product Approval


[Miscellaneous](#)

[China RoHS](#)


## General Product Approval

## For use in hazardous locations


[Declaration of Con-  
formity](#)


## For use in hazardous locations

## Maritime application


[Miscellaneous](#)


## Maritime application

## Environment


[NK / Nippon Kaiji Ky-  
okai](#)

[CCS \(China Classifica-  
tion Society\)](#)

Siemens  
EcoTech



last modified:

7/3/2025