

Features

- Inox flush cutter for the cutting of copper wire and other soft materials.
- Made by stainless steel.
- Inox steel thickness 2.5 mm.
- For copper wire Ø 1.30 mm (16 awg)
- Tool is equipped with a return spring designed to have a constant force, thus reducing operator effort.
- Ergonomic anti-slip bicomponent handle for a safe, light and comfortable grip.
- ESD-safe handles.
- Laser marking.
- Made in Italy.

RS PRO ESD Flush cutter made by stainless steel. Medium head.

Manufacturer Stock No.: (0429720)



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

- *Made in Italy by stainless steel offers a high resistance to corrosion, is wet resistant and has a high durability. Thanks to its smooth surface, stainless steel, tends to retain polluting impurities in smaller amounts than others so that it is suitable to be used for applications in clean-room, electronics applied to medical industry and fish industry as well.*
- *Inox flush cutter for copper wire max Ø 1.30 mm (16 awg)*
- *The tools are joined with grounded holes and surfaces, thereby allowing precise movements.*
- *The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator even when used constantly for many hours.*
- *ESD-safe version.*

General Specifications

Cutter Type	Flush cutter made by stainless steel. Medium head.
Material	Stainless steel
ESD Safe	YES. Standard IEC 61340-5-1

Mechanical Specifications

Cutting capacities	Ø 1.30mm (16 awg) copper wire
Cutting force	5 kg
Steel thickness	2.5 mm
Blade angle	27°
Overall Length	138 mm +/-2 mm
Weight	73 g +/-2 mm

