


AFJ, Vacuum Filter AFJ30-F03-5-S

Datasheet

General series information

- Large flow type AFJ-T, up to 660 l/min, for dust removal.
- Water drop removal type AFJ-S, up to 500 l/min, for both dust and water droplets removal.
- Filtration rating: 5, 40, 80 µm.
- Port sizes: from 1/8 to 1/2.
- Standard options: bracket; bowl material, selectable flow direction.




Standard specifications

Body Size	30
Pipe Thread	F (G)
Port Size	03 (3/8)
Mounting	w/o Mounting Option
Nominal Filtration Rating	5 (5µ)
Type	S (Water Drop Removal Type)
Semi-standard	None
Pressure medium	Air
Maximum temperature of pressure medium	60 °C
Minimum temperature of pressure medium	-5 °C (with no freezing)
Maximum operating pressure	0 KPa
Minimum operating pressure	-100 kPa
Proof pressure	0.5 MPa
Maximum ambient temperature	60 °C
Minimum ambient temperature	-5 °C (with no freezing)
Conform to the European RoHS Directive	Conform
Bowl Material	Polycarbonate
Bowl Guard	Polycarbonate

Drain Capacity	25 cm ³
Flow rate	230 l/min
ISO 8573 compliant	No
Approvals	No need
Weight	0.178 Kg

Dimensions



Additional information

Catalogue

[AFJ-A_EU.pdf](#)