


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
E	C210309	2021/02/24	Ruru	X2
F	C221973	2022/12/21	Ruru	X1
G	C231034	2023/08/08	Ruru	X1







Recommended
Panel Cut-Out



MI2A-XXPFFS-SH8001

XX: No. Of Pin



Note:


- * RoHS Compliant
- * Important dimension
- * Waterproof rate: IP68, unmated 1m/24h
IP69K, mated
- * Connector
Housing: Thermoplastic, Black
Pin: Copper alloy, Gold plated
O-Ring: Rubber, Green
- * Shield: Metal
- * Nut: Metal
- * O-Ring: Rubber, Black
- * For panel thickness max: 4.5mm
- * Nut is packed separately in pe bag



MI2A-03PFFS-SH8001		2.5	
MI2A-04PFFS-SH8001		2.5	
MI2A-05PFFS-SH8001		2.5	
MI2A-06PFFS-SH8001		2.5	
MI2A-08PFFS-SH8001		2.5	
MI2A-10PFFS-SH8001	4.5	2.5	
MI2A-12PFFS-SH8001	4.5	2.5	
MI2A-17PFFS-SH8001	4.5	2.5	6.5


Item No.

Pin伸出長度



Pin Assignment Front View

UNIT:mm



TITLE
N SEN, MI2 A, SCREW
RECEPTACLE, F, F, SOLDER

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO.	DRAWN BY	DATE
DWG. NO.	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE



MI2A-XXPFFS-SH8001

ALTW

Jinhai

Jerry

2016-08-05

2016-08-05

2016-08-05

2016-08-05