

FEATURES

- **Black Neoprene Rubber**
- **Flexible**
- **Durable**
- **Customisable**
- **Resistant to ozone, sunlight and atmospheric ageing**

RS PRO Black Rubber Sheet, 1m x 600mm x 10mm

RS Stock No.: 506-3135



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Introducing a series of neoprene rubber sheets from RS PRO. These black neoprene rubber sheets are suitable for use, both indoor & outdoor, offer moderate resistance to atmospheric ageing, sunlight, oils, and greases.

RS PRO Rubber Sheet Options

- 1 m x 600 mm x 1.5mm - RS Stock no: 506-3163
- 1 m x 600 mm x 3mm - RS Stock no: 506-3157
- 1 m x 600 mm x 6mm - RS Stock no: 506-3141
- 1m x 600mm x 12mm - RS Stock no: 506-3113
- 1 m x 600 mm x 10mm - RS Stock no: 506-3135
- 1 m x 1.2 m x 1.5mm - RS Stock no: 506-3107
- 1 m x 1.2 m x 3mm - RS Stock no: 506-3208
- 1m x 1.2m x 6mm - RS Stock no: 506-3191
- 1m x 1.2m x 10mm - RS Stock no: 506-3185
- 1m x 1.2m x 12mm - RS Stock no: 506-3179

General Specifications

Colour	Black
Suitability	Animal Oil; Cold Water; Dilute Acid; Dilute Alkali;
Elongation	300%
Hardness	60+/-7
Finish	Smooth
Durometer	Shore A
Density (Gram/cm³)	1.35
Application	Sound-proofing, Noise and Heat insulation

Mechanical Specifications

Length	1m
Thickness	10mm
Width	600mm
Tensile Strength	5N/mm ²

Operation Environment Specifications

Maximum Operating Temperature	70°C
Minimum Operating Temperature	-10°C