



Brand of NTN corporation

## Technical data

### UCEHE.204

Bearing units




Grey cast housing, radial insert ball bearing with socket set screws, seal with slinger

#### KIT CONTENT

UC204G2, EHE204

#### VISUAL (S)



#### PRODUCT DEFINITION

<b>Brand</b>	SNR
<b>A - Housing width</b>	25 mm
<b>A2</b>	30 mm
<b>B - Width of Inner Ring</b>	31 mm
<b>d - Shaft diameter</b>	20 mm
<b>E - Mounting hole thread depth</b>	21 mm



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

### PRODUCT DEFINITION

<b>G - Grease fitting</b>	R1/8"
<b>G1 - Thread size</b>	M16
<b>H - Housing length, width or diameter</b>	65 mm
<b>L - Housing length</b>	91 mm
<b>L1 - Distance attachment end face to bearing centerline</b>	58 mm
<b>L3 - Length of guidance slot/face</b>	38 mm
<b>S - Distance front side/bearing centre</b>	12,7 mm

### PRODUCT PERFORMANCE

<b>C - Dynamic load rating</b>	12800000 mN
<b>C0 - Static load rating</b>	6650000 mN
<b>Operating temperature min.</b>	253,15 °K
<b>Operating temperature max.</b>	373,15 °K

### OTHER FEATURES

<b>Mass</b>	0,57 kg
<b>Recommended tightening torque for set screw</b>	5.5 N-m

