

## Technical data sheet

**Article number:**  
**924-00398**

**SD5-5**

|                                                |                                      |
|------------------------------------------------|--------------------------------------|
| <b>Product Group</b>                           | Spade/Forks Terminals                |
| <b>Product Family</b>                          | Double Grip Pre-Insulated            |
| <b>Material</b>                                | Copper (CU), Polyvinylchloride (PVC) |
| <b>Colour</b>                                  | Yellow (YE)                          |
|                                                |                                      |
| <b>Application Range</b>                       | Low Voltage                          |
| <b>Conductor Size Range mm<sup>2</sup></b>     | 4.0-6.0 mm <sup>2</sup>              |
| <b>Diameter (D)</b>                            | 6.7 mm                               |
| <b>for Hole Ø (FH)</b>                         | 5.3 mm                               |
| <b>Length (L)</b>                              | 26.2 mm                              |
| <b>Length (L2)</b>                             | 13.6 mm                              |
| <b>Length (L3)</b>                             | 12.6 mm                              |
| <b>Max Current</b>                             | 48 A                                 |
| <b>Max Voltage</b>                             | 600 V                                |
| <b>Operating Temperature</b>                   | +75 °C                               |
| <b>Package Content</b>                         | 50 pcs.                              |
| <b>Package Content packed in</b>               | bag                                  |
| <b>REACH Reg. Art.33 does not contain SVHC</b> | Yes                                  |
| <b>ROHS compliant</b>                          | Yes                                  |
| <b>Width (W)</b>                               | 9 mm                                 |

**RoHS** 