

General Information

Extended Product Type:	MTC6
Product ID:	1SNA115206R2200
EAN:	3472591152067
Catalog Description:	MTC6 Screw Clamp Terminal Blocks - Thermocouple - Grey
Long Description:	- MTC 6 thermocouple terminal block provides an interface for connecting thermocouple wire with virtually no loss of signal integrity, - The interface design ensures positive wire continuity and allows selection and inventory of one terminal block for all thermocouple material.

Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Ambient Temperature:	-5 ... +40 °C
Color:	Grey
Connection Type:	Screw clamp
Country of Origin:	France (FR)
Customs Tariff Number:	85369010
Data Sheet, Technical Information:	1SNC160020C0201
Declaration of Conformity - CE:	1SND225051U1000
EAC Certificate:	1SND161009A1100
EAN:	3472591152067
ETIM 4:	EC000904 - Thermal couple terminal block
ETIM 5:	EC000904 - Thermal couple terminal block
ETIM 6:	EC000904 - Thermal couple terminal block
Environmental Information:	1SND220005E1002
Flammability According to UL94:	V0
Function:	Thermocouple
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160020C0201
Insulation Material:	Polyamide
Invoice Description:	MTC6 Screw Clamp Terminal Blocks - Thermocouple - Grey
Minimum Order Quantity:	50 piece
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Connections:	2
Number of Levels:	1
Object Classification Code:	X
Order Multiple:	50 piece
Package Level 1 EAN:	3472591152067
Package Level 1 Gross Weight:	1 kg
Package Level 1 Height:	47 mm
Package Level 1 Length:	220 mm
Package Level 1 Units:	50 piece
Package Level 1 Width:	61 mm

Package Level 2 Units:	1000 piece
Package Level 3 Units:	48000 piece
Pollution Degree:	3
Product Main Type:	MTC6
Product Name:	Terminal block
Product Net Depth:	40.5 mm
Product Net Height:	44.5 mm
Product Net Weight:	20 g
Product Net Width:	6 mm
Product Packing Type:	Box
Rated Cross-Section:	1.5 mm ²
Rated Voltage (U_r):	500 V
RoHS Date:	20050518
RoHS Information:	1SND230023F0208
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Selling Unit of Measure:	piece
Short Description:	grey Screw Clamp Terminal Blocks MTC6 pour raccordement de thermocouple
Spacing:	6 mm
Tightening Torque:	acc. IEC 60947-1 0.4 N·m Manufacturer 0.6 N·m
Wire Stripping Length:	31.0 mm
Number of Potentials:	1

