

Previously known as: Oceanic<sup>®</sup> 48-913



Oil



Medium Duty

## Medium-duty, nitrile-coated safety gloves, providing abrasion, oil and liquid resistance

- **Increased defenses:** These economical yet high-quality industrial gloves offer good resistance to abrasive materials and are lighter and more flexible than Hycron<sup>®</sup> 27-607 nitrile-coated gloves
- **Heightened protection:** Owing to their nitrile coating, EDGE<sup>®</sup> 48-913 protective gloves are hardy and deliver long-lasting performance and defend against hazardous oils and liquids, making them ideal for medium-duty applications
- **Elevated comfort:** Made of cotton jersey liner, these nitrile-coated knit gloves offer breathable comfort and greater flexibility
- **Food handling compliance:** Composed of FDA-approved materials, these hand protection gloves are safe for food contact and packaging



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Recycling and Waste Disposal

### Applications

- Cold plastic moldings
- Heavy-duty cables
- Rough casting and cores
- Steel bars, sheet metals, cans and other metal products
- Street cleaning and refuse collection

Previously known as: Oceanic<sup>®</sup> 48-913

### Key Features

- **Mechanical performance:** Good level of protection against abrasions
- **Nitrile coating:** Durable work gloves, guarding against oils and liquids
- **Cotton jersey:** For lightweight, flexible and comfortable work gloves

### Performance Standards & Regulatory Compliance



EN388: 2016



3111B

### Specifications

| BRAND   STYLE            | DESCRIPTION                                                                                                                              | Gauge | SIZE         | LENGTH     | COATING COLOR | PACKAGE                      |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------------------|-------|--------------|------------|---------------|------------------------------|
| EDGE <sup>®</sup> 48-913 | <b>Finishing:</b> ¾ Dipped<br><b>Coating Material:</b> Nitrile<br><b>Liner Material:</b> Cotton Jersey<br><b>Cuff Style:</b> Safety Cuff |       | 8, 9, 10, 11 | 235-270 mm | Blue          | 12 pairs/bag, 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699