



ENGLISH

Datasheet

UKAS 2 Output Switch Mode DIN Rail Panel Mount Power Supply, 12 V, 24 V, 5 V, 1 A, 1.5 A, 2.5 A

RS Stock 537-7793



Specification:

A405 LABORATORY POWER SUPPLY	
Input Voltage	230V \pm 10%
Input Frequency	50/60 Hz
Output Voltages	5V \pm 0.05V
	12V \pm 0.05V
	15V \pm 0.05V
Output Currents	2.5 A maximum
	1.5 A maximum
	1 A maximum
Operating Temperature	0 to 40°C
Load Regulation	<10mV
Dimensions	210 mm x 210 mm x 80 mm
Weight	3.0 kg

Series connection:

Several combinations of positive and negative power rails, such as \pm 5V, \pm 12V etc., may be obtained, at currents up to the rated limit, by connecting the positive terminal of one output to the negative terminal of the other output with the junction being at '0V'.

Parallel Connection:

Current may be increased by connecting the two outputs in parallel.