



## **Datasheet**

## RS PRO 6m D25 Way M to D25 Way female Straight Through Cable - 5 Pack


Stock number: 2513285

EN

Our RS PRO 6m D25 male to D25 female is wire pin to pin has a beige PVC cable flex.

The connector hoods are made from beige PVC and have a strain relief on the end of the hood to support the cable and to stop the cable from splitting around the hood.

The cable flex has an outer diameter of 7mm and 30awg, the connectors have gold flash pins to help stop corrosion.



	Ρ1	P2	P1	P2	
BROWN	1	1	14	14	BROWN/BLACK
RED	2	 2	15 ———	<del> 15</del>	RED/BLACK
ORANGE	3	 3	16 —	16	ORANGE/BLACK
PINK	4	 4	17 ———	<del></del>	PINK/BLACK
YELLOW	5	5	18	18	YELLOW/BLACK
GREEN	6	6	19 ———	<del></del>	GREEN/BLACK
LIGHT GREEN	7	7	20 ———	—— 20	LIGHT GREEN/BLACK
BLUE	8	8	21 ———	21	BLUE/BLACK
LIGHT BLUE	9	 9	22	—— 22	LIGHT BLUE/BLACK
PURPLE	10	10	23 ———	23	PURPLE/BLACK
GREY	11	11	24		GREY/BLACK
WHITE	12	12	25 ———	—— 25	WHITE/BLACK
BLACK	13	13	SHIELD -	- SHIE	LD

5	BLACK PVC TUBE ø3.0*30mm				
	ALUMINUM FOIL 33*110mm				
	MOLDED PE COLOR TRANSPARENT				
	MOLDED PVC BEIGE				
4	NON-UL 25C 30AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 7.0mm, JACKET BEIGE				
3	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BEIGE				
2	DB25 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR				
1	DB25 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR				

**RoHS / REACH / CE /UKCA**