


1440/...

piston ring compressors

	art.	Ø mm	L mm	g
014400000	1440/0	40÷75	50	140
014400010	1440/1	57÷125	80	250
014400011	1440/1A	57÷125	100	300
014400020	1440/2	90÷175	80	270
014400021	1440/2A	90÷175	100	300
014400030	1440/3	90÷175	165	500

