



Main

Range of product	Mita
Product name	Cableline 50 Ultimate 60 Cableline 40 Ultimate 62
Product or component type	Mounting box
Colour tint	White
Quantity per set	Set of 10

Complementary

Trunking dimension	145V x 40 mm 145 x 40 mm 180V x 52 mm 150 x 60 mm 180W x 52 mm 145W x 40 mm 180 x 52 mm 190 x 62 mm
Number of gangs	2 gangs
Mounting support	Trunking
Device mounting	Flush
Material	UPVC (unplasticized polyvinyl chloride)
Depth	25 Mm

Environment

Standards	EN 50085-1: 2005 EN 50085-2-1
Ambient air temperature for operation	-5...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	52 G
Package 1 Height	2.6 Cm
Package 1 width	8.7 Cm
Package 1 Length	14.2 Cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**