



## Overview

Lead time	Usually in Stock
-----------	------------------

## General

Provided equipment	User manual Warranty card
--------------------	------------------------------

## Physical

Colour	Black
Depth	38.2 cm
Height	30.1 cm
Net weight	13.4 kg
Width	11.2 cm

## Environmental

Ambient air temperature for operation	0...30 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m

## Batteries & Runtime

Number of battery free slots	0
Number of battery filled slots	0
Device mounting	Stand alone battery stack
Battery voltage	24 V
Battery type	Lead-acid battery
Number of battery replacement quantity	1

### Packing Units

Package 1 Weight	14.6 kg
Package 1 Height	38.1 cm
Package 1 width	22.9 cm
Package 1 Length	48.3 cm
SCC14	10731304286254

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

### Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------