

GHO 16-82 D Professional

Wood Planer

**Door trimming and more
made easy**



Specification	
Power	630 W
Cutting depth	1.6 mm
Cutting width	82 mm
No-load speed	18,000 rpm
Chip eject	Right
Cord length	4 m
Weight	2.8 kg
Length	372 mm
Width	192 mm
Height	184 mm
Part number	0.601.5A4.070

Key Product Features	Consumer Benefit
Powerful motor	630 W motor
Sturdy	Sturdy, flat aluminium base plate for the best planning results
Lock-out button	Prevents unintended start
Soft grip handle	For convenience and comfort
Spring loaded park shoe and improved front shoe	This gives protection to the material surface and offers more stability
Cutting depth	Adjust the cutting depth in 0.1mm steps up to 1.6mm



You Tube youtube.com/BoschProfessionalUK

f facebook.com/BoschProfessionalPowerToolsUK



BOSCH

Invented for life

* Please register your tool, lithium-ion battery or charger online within four weeks of purchase to become eligible for the warranty services Bosch provide