



ENGLISH

Datasheet

Stock No: 282-3489

# RS Pro 51 bar 2000mm Long Copper Pipe, 22mm Outer Diam. Chrome Plated



## Product Details

### Chromium Plated Copper Tube

Electroplated generally in accordance with BS 1224: 1970 service condition 2

Supplied in 2m straight lengths in the half hard condition

Pressure rating (see table) based on tube in half hard condition at 65°C

Ideal for cold bending either on a bending machine or with correct size bending spring

Used where a decorative finish is required for exposed pipework

### Straights & Coils



ENGLISH

## Specifications

Nominal Outer Diameter	22mm
Length	2000mm
Wall Thickness	0.9mm
Maximum Working Pressure	51 bar
Finish	Chrome Plated