

# CONTACTUM



## DDS12188SPMS



### Surge Device Spec:

Uc - 275V

In - 10kA

Imax - 20kA

Up - ≤1.2kV

Green (ok) Red (replace) status indicator

12 Way H/Int 100A Sw+2x80A RCD+SPD CU

### General

**Box quantity:** 1

**ABC indicator:** A

**Colour:** White

**Fault current protection (RCD):** Yes

### Technical

**Associated standards:** BS EN 61439-3

**Rated voltage:** 220-250V

**Rated current:** 100A

**Frequency:** 50-60Hz

**Wiring system:** 2 pole

**Ambient operating temperature:**

-5 to 40°C (24hour average not exceeding 25°C)

**Width in number of modular spacings:** 20

**Nature of supply:** AC

**Rated fault current:** 30

**DIN-rail:** Yes

**Extension possible:** Yes

**With lock:** Optional

**Type of cover:** Hinged

**Material housing:** steel

**Plate thickness cabinet:** 1.2mm

**Plate thickness door/cover:** 1.2mm

**Mounting method:** Surface

**Number of outgoing ways:** 12

Copyright © 2017 Contactum Limited, Victoria House, 2 Blackmoor Lane, Croxley Green Business Park,  
Watford, WD18 8GA

**Source URL:** <https://www.contactum.co.uk/content/dds12188spms>