



MINI ORBITAL SANDER 50-75MM

RC1346C

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:11:58





DESCRIPTION

MINI ORBITAL SANDER 50-75MM

Orbital sander for touching up small surfaces (spot repair). Composite body. The sander is mounted on Ø 50 and 75 mm backing pads. This reference is supplied with Ø 75 mm backing pads. Handle with grip. Progressive trigger. Variable speed control and rear exhaust. Lightweight, ergonomic tool well insulated against the cold.

STANDARDS / DIRECTIVES

2006/42/CE, ISO 11148-6, ISO 15744, ISO 28927-2

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:11:58



SPECIFIC DATA

Designation	MINI ORBITAL SANDER 50-75MM
Sales reference	RC1346C
L (mm)	115
Weight (g)	800
l (mm)	40
h (mm)	90
Power (W)	
Rotation speed (rpm)	15 000
Vibration (m/s²)	2,5
Noise level (dBa)	80
C mm	6,3
C min mm	1/4"
C mm	4
Eccentricity (mm)	50-75
Tray Ø (mm)	
Guarantee	M2 SAM Equipment and Machine Guarantee

Guarantee applied

M2 | SAM Equipment and Machine Guarantee

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:11:58

