



Passive Components > Resistors > Surface Mount Resistors > Thick Film Resistor: Current Sense



Resistance Value: .047 Ω

Resistor Type: **Current Sensing Resistor**

Element Type: **Thick Film**

Package Size Code: **2512**

Power Rating: **2 W**

[All Thick Film Resistor: Current Sense \(142\)](#)

Features

Product Type Features

Resistor Type	Current Sensing Resistor
Element Type	Thick Film
Package Size Code	2512

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Resistance Value	.047 Ω
Power Rating	2 W
Resistance Class	Up to 1kΩ
Passive Component Tolerance	5 %

Termination Features

Surface Mount Resistor Termination Type	Solder
---	--------

Number of Terminations

2

Dimensions

Product Height	.74 mm[.029 in]
Product Length	6.35 mm[.25 in]
Product Width	3.15 mm[.124 in]

Usage Conditions

Temperature Coefficient	±400 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

RLP73M3AR047JTDG

.047 ohm, Surface Mount Current Sensing Resistor, Thick Film, 2512, 2 W, 5 %, ±400 ppm/°C, Solder, 2 Terminations, .74 mm [.029 in] Height, CGS RLP73



TE Part # 2176050-8
RLP73N 1E R10 5% 5K RL

TE Part # CAT-C339-R529A
Thick Film Resistor: Current Sense

Also in the Series | CGS RLP73

Surface Mount Resistors(337)

Customers Also Bought

TE Part #101789-000
22759/34-24-6

TE Part #1622258-1
LR0204 1% 5K1

TE Part #1776275-8
8P TB ,90deg,VT,3.5mm,Blue,w /interlock

TE Part #4-1879022-9
SMF3 33K 5%

TE Part #1658621-1
10 NOVO MIL/CTR 15DP,LEAD FREE

TE Part #3-1761713-3
IDC LOW PRO HDR 40P VERT SHT L

TE Part #1-87499-1
06 MODIV HSG SR MRKD .100CL

TE Part #2311402-3
CAP,RD, ILLUMINATED TACT SWITCH, RED

TE Part #9-2176398-5
3502 100R 5%

TE Part #2-5435668-5
DIP SW 6 POSN W/TAPE AU



Documents

Product Drawings

RLP73M 3A R047 5% 2K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2176058-7_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2176058-7_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2176058-7_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD Low Ohmic Current Sense Resistors - Type RL73 Series

English